

### Main

Commercial Status	Commercialised
Range of product	Easy9
Product or component type	Consumer unit with incomer
Enclosure type	Split board
Provided equipment	2 residual current device (RCD) 80 A Earth/Neutral terminal block 1 switch-disconnector 100 A
Type of front cover	Opaque
Product compatibility	Easy9 MCB Easy9 RCCB Easy9 RCBO Easy9 switch

### Complementary

Enclosure mounting	Surface
Number of 18 mm modules per row	16
Total number of 18 mm modules	16
Number of horizontal rows	1
Number of ways	RCD 2[ way x ] 7 RCD 1[ way x ] 7 Switch[ way x ] 2
Enclosure material	Insulating material
[In] rated current	100 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Type of rail	DIN
Cable entry	Knock-out
Downside connection	Rear
Cable cross section	1...25 mm <sup>2</sup> incoming
Comb busbar and distribution block compatibility	YES
Height	240 mm
Width	510 mm
Depth	127 mm
Colour	White ( RAL 9003 )

### Environment

Standards	BS EN 61439-3
-----------	---------------