



ENGLISH

Datasheet

Stock No: 196-5009

# RS Pro Swivel Plate Castor, 150kg



## Product Details

Elastic Rubber Tyre, Heavy Duty Castor

Ball bearing hub



ENGLISH

## Specifications:

Wheel Diameter	100mm
Load Capacity	150kg
Overall Height	132mm
Wheel Width	40mm
Fixing Plate Dimensions	100 x 85mm
Rotation	Fixed
Tyre Material	Rubber
Fixing Centres	80 x 60mm
Weight Class	Heavy Duty
Features	Shock Absorbing
Number of Fixing Holes	4
Fixing Hole Size	8.5mm
Fixing Plate Length	100mm
Fixing Centres Width	60mm
Fixing Centres Length	80mm
Hub Material	Aluminium
Fixing Plate Width	85mm
Hub Bearing Type	Ball Bearing