

Features

- Optimised modular 50mm diameter signal tower in a white housing
- Pre-assembled with 4 modules, red, amber, green & blue
- LED steady beacon functionality on each module
- Tube mounting 100mm
- Supply voltage 24V DC

RS PRO Beacon Signal Towers

0694282



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- Modular 50mm diameter signal tower in white
- Pre-assembled LED steady beacon signal tower with 4 modules
- Preconfigured with Red, Amber, Green and Blue LED modules.
- Light source > 100,000 hours
- Up to a maximum of 5 modules can be fitted
- Tube mounting (100mm)
- Optimised 'resilient' bayonet system enables high stability, even without sealing rings
- Five-pole M12 base with automatic contacting push-in system
- All common mounting types. Can be mounted horizontally, vertically, tube mount or NPT ½"

General Specifications

Lens	Polycarbonate, ribbed inside
Bulb Type	LED
Light Effect	Steady
Lens Colour	Red, Amber, Green and Blue
Fitting	Tube mount. White base. 100mm
Lamp Include	Yes
Protection	Against water & dust, vibration (IK07)

Electrical Specifications

Supply Voltage	24V DC
Current Type	DC

Mechanical Specifications

Dimensions	50mm (w) x 50mm (d) x 340mm (h)
Mounting Style	Screw Mount
Weight	262g

Operation Environment Specifications

Maximum Temperature	+60°C
Minimum Temperature	-30°C

Protection Category

IP Rating	IP65
------------------	------

Approvals

Compliance/Certifications	CE / UL
Declarations	RoHS Compliant / REACH
Standards Met	Yes
Hazardous Area Certification	N/A