

Han-Power T 3x Han 3A compl. assembled



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 008 4750
Specification	Han-Power T 3x Han 3A compl. assembled
HARTING eCatalogue	https://harting.com/09120084750

Identification

Category	Energy distributors
Series of hoods/housings	Han-Power® T
Element	Energy distributor
Specification	with 3x Han® 3 A In Han® 3 A Housings, bulkhead mounting

Version

Number of contacts	3
PE contact	Yes

Technical characteristics

Rated current	10 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 ⁸ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP44 IP67 with seal screw 09 20 000 9918



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Polyamide (PA)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
ECHA SCIP number	564b7d75-7bf6-4cfb-acb1-2168eb61b675
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	1
Net weight	69.8 g
Country of origin	Mexico
European customs tariff number	85366990
GTIN	5713140190573
eCl@ss	27142409 Small distribution board
ETIM	EC000214
UNSPSC 24.0	39121303