

8008TZN**Stub and stub turnbuckles, pipe bodies DIN 1478, self-coloured terminals, galvanised bodies**

CE

TECHNICAL DATA

- safety factor: 4

LABORATORY TESTS

- chemical analysis
- tensile test

AVAILABLE CERTIFICATES

- Product specifications
- Test report type 2.2 UNI EN10204
- CE Declaration of Conformity



	art.	Ø mm	≈ "	WFL kg
080080512	8008TZN M12	M12	1/2	690
080080516	8008TZN M16	M16	5/8	1290
080080520	8008TZN M20	M20	3/4	2130
080080524	8008TZN M24	M24	1	3060
080080527	8008TZN M27	M27	1.1/8	4000
080080530	8008TZN M30	M30	1.3/16	4860
080080536	8008TZN M36	M36	1.3/8	6500