

Hot air tool - Professional Line

PRO HM 2320 ESD

EAN 4007841 091347

Article number 091347

 steinel



series 5



Timer function

2300 W

2300 W Output

Display

Display (LCD)



80 - 650°C



stepless adjustable



150 - 500 l/min.



Suitable for
pluggable nozzles



VDE



CE

Function description

Precision digital control. Electronically controlled HM 2320 E hot air tool. 2300 W, digital temperature setting by joystick from 80 – 650 °C, temperature indicated in 10 °C steps on LCD display. Airflow regulation in 2 stages of 150 and 500 l/min. ESD-compliant, meets the requirements defined in IEC DIN EN 61340-5-1; part 5-1:2008 ff.

Technical specifications

Temperature	80 – 650 °C	Replaceable heating element	No
Airflow rate	150 – 500 l/min	Restart protection	No
Temperature setting	in 10°C steps by joystick	Temperature scanner	Yes
Settings made via	joystick	Fine dust filter	No
Temperature display	LCD display	Thermal cut-out	Yes
Airflow control	Settings	Thermostat	Yes
Programming function	Yes	ESD	Yes
Loc function	Yes	Nozzle receiver, type	34
Residual heat indicator	Yes	Cord length	3 m
Cool function	No	Dimensions (L x W x H)	253 x 87 x 200 mm
Motor, type	Brush motor	PU1, net weight	1,004 kg
Heating element	Ceramic heating element	Manufacturer's Warranty	1 year
Mains power supply	230 V / 50 – 60 Hz	PU1, EAN	4007841091347
Function, hanger	Yes	Output	2300 W
Function, life expectancy, motor	1000 h	Product category	Hot air tool
Function, life expectancy, heating element	600 h		

<https://www.steinel.de/en/>

Subject to technical modifications

04.2026 Page 1 from 2

PRO HM 2320 ESDEAN 4007841 091347
Article number 091347**Accessories**

EAN 4007841 074616	Soldering reflector nozzle 14 mm
EAN 4007841 034566	HL Tool Stand
EAN 4007841 010294	Sieve reflector nozzle 50 x 35 mmT421T399:T827
EAN 4007841 009571	Reduction nozzle 6 mm
EAN 4007841 075569	12-piece hot-air accessory kit
EAN 4007841 070618	Reduction nozzle 9 mm
EAN 4007841 073114	Plastic welding rod PVC
EAN 4007841 006648	Crimp connectors Ø 1,5 - 2,5 mm (10 ea.)
EAN 4007841 072766	Shrink tubing III Ø 4,8 - 12,0 mm
EAN 4007841 006662	Crimp connectors - Ø 0.1 - 6.0 mm 10 ea.
EAN 4007841 071318	Shrink tubing I Ø 1,6 - 4,8 mm
EAN 4007841 006655	Crimp connectors Ø 0,5 - 1,5 mm (10 ea.)
EAN 4007841 070717	Reduction nozzle 14 mm
EAN 4007841 006785	Pressure roller Silicone Ø 35 mm 40 mm
EAN 4007841 074210	Plastic welding rod ABS
EAN 4007841 009601	Flexible hot air tool stand with suction pad foot
EAN 4007841 071417	Shrink tubing II Ø 4,8 - 9,5 mm
EAN 4007841 070212	Surface nozzle 75 mm
EAN 4007841 075811	Shrink tubing kit
EAN 4007841 010317	Paint Scraper Set
EAN 4007841 070915	Welding nozzle
EAN 4007841 070113	Surface nozzle 50 mm
EAN 4007841 070311	Window nozzle 50 mm
EAN 4007841 014919	Temperature scanner HL Scan
EAN 4007841 070519	Reflector nozzle
EAN 4007841 009595	Flexible hot air tool stand with magnetic foot
EAN 4007841 034122	Pressure roller 40mm - Teflon
EAN 4007841 073411	Plastic welding rod PP
EAN 4007841 070410	Window nozzle 75 mm
EAN 4007841 071219	Plastic welding rod HDPE
EAN 4007841 093211	Pressure roller 50mm - Rubber
EAN 4007841 074715	Wide-slit nozzle
EAN 4007841 078218	Fine dust filter HL 1920 E - HG 2320 E Singlepack
EAN 4007841 053963	Hot Air Tool Guard Cage HL 1820 S - HG 2320 E