


Gear unit

EMGA-80-A-G3-80P

Part number: 8085346

FESTO



 General operating condition

Data sheet

Feature	Value
Gear unit flange size	80 mm
Motor flange size	80 mm
Torsional backlash	0.22 deg
Type of gear unit	Right-angle gear unit
Gear unit ratio	3:1
Max. drive speed	7000 rpm
Operating temperature of gear unit	-25 °C ... 90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP54
Continuous output torque	40 Nm
Mass moment of inertia of gear unit	1.409 kgcm ²
Max. output torque	64 Nm
Max. efficiency	95 %
Torsional rigidity	5 Nm/arcmin
Product weight	4300 g
Gear unit interface, output shaft	80G
Gear unit interface, drive shaft	80P
Note on materials	RoHS-compliant