


PX0575/30/PC Datasheet

 [View Product Page](#)

**Product Name // IEC Connector PCB Mount Snap Fit To
Panel Inlet PX0575 Series 3mm Panel Black No Cover PCB
Spills Termination EN60 320-1 Standard Sheet C14 Class I**



// Product Description:

- Snap Fit Panel Mount IEC Inlets
 - EN60 320-1 Standard Sheet C14 Class I
 - Cold Condition
 - Choice of panel thickness depending on part code: /10 - 1mm, /15 - 1.5mm, /20 - 2mm, /30 - 3mm
- Choice of Termination depending on part code: /28 - 2.8mm Solder Tag, /48 - 4.8mm Tab, /63 - 6.3mm Tab, /TERM - Screw Terminal, /PC - PCB Spills
 - Choice of colour depending on part code: /WH - White, /GY - Grey, no suffix - Black (some approvals apply to specific colour only - see data for details)
 - PCB Mount version (part codes containing /PC) available with rear cover (part codes suffixed /C), for all other versions Insulation Boot for rear of connector available separately (part code 11328)
 - Mate with PX0587, PX0587/SE, PX0588

// General Information:

Product Display Title:	Snap Fit Panel Mount IEC Inlets
Product Family:	IEC Connectors
Product Series:	IEC60320 Main Inlets and Outlets
Approvals:	CSA, ENEC, UL, VDE, CCC
Body Material:	Nylon 66
Current Max:	10A, 15A
Flamability Rating:	UL94V-0
Function:	Panel Mount Connector
Iec Connector Colour:	Black
Iec Connector Mates With:	PX0587,PX0587/SE,PX0588
Iec En60620 Type:	EN60 320-1 Standard Sheet C14 Class I
Iec Pcb Rear Cover:	No Cover
Max Operating Temperature:	+70°C
Min Operating Temperature:	-40°C
Max Panel Thickness:	3mm
Min Panel Thickness:	3mm
Number Of Contacts:	3 Contacts
Voltage Max:	250V

// Product PDF Links

 [IEC Connectors product data](#)

// Product 3D CAD Model Links

 [PX0575/30/PC3D CAD Model](#)



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)