



Oil



Heavy Duty

Heavy-duty nitrile-coated safety gloves, ensuring abrasion-resistant mechanical protection

- **Enhanced durability:** ActivArm® Hycron® 27-607 nitrile-coated protective gloves are stronger and more flexible than PVC, and three times tougher than heavy-duty leather alternatives that meet ANSI/ISEA 105-2024 and EN ABRASION LEVEL 4 standards, providing excellent protection against grease and oil.
- **Elevated comfort:** Unlike standard leather and cotton alternatives, these user-friendly cotton jersey-lined work gloves do not degrade easily, protecting hands and enhancing comfort levels with better perspiration relief and a cushioned feel
- **Reduced surface defects risks:** ActivArm® Hycron® 27-607 industrial gloves' silicone-free composition ensures they are reliably fit for purpose, suitable for both metal and motor manufacture applications



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- Handling metal sheets & panels
- Metalworking & assembly operations
- Press injection molding
- Seizing and finishing structural parts
- Fixing, clipping parts and wire harnesses; connecting devices
- Assembly & inspection of components

Key Features

- **Unique nitrile formulation:** For genuinely abrasion-resistant gloves*
- **Cotton jersey liner:** For highly comfortable, breathable work gloves
- **Silicone-free design:** Suitable for metals and motor manufacture

*3x greater durability than standard leather alternatives

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4121B

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm®Hycron® 27-607	Finishing: ¾ Coated Coating Material: Nitrile Liner Material: Cotton Jersey Cuff Style: Safety Cuff		8, 9, 10, 11	246-272 mm/ 9.68-10.70 inches	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699