

GRINDER DUO 125/230 MM

- Powerful motor protected against abrasive particles for longer life
- Two-position side handle for better comfort of use
- Shaft lock for quick and easy disc changes
- Specific opening for quick replacement of the brushes

Grinder 2200W 230 mm DWE492

No-load speed 6600 rpm

Weight 5.2 kg

+Grinder 900W 125 mm DWE4157

No-load speed 11800 rpm

Weight 2.1 kg



with protective guard, 2-position side handle,
indoor/outdoor flange, service key, case

DWE492TWIN2-QS

5 035 048 655 009