

Datasheet

RS Pro 8mm Plain Stainless Steel Aerotight Locking Nut, M5, 316, A4

RS Stock No: **665-5603**



Product Details

RS Pro self locking aero tight stiff nut has a type-316, A4 grade stainless steel construction for corrosion resistance. The nut is designed to stay in position despite conditions of severe vibration. This 8 mm locking nut features M5 metric threads to stays in position, whether tightened or not. The nut is suitable for use in highly corrosive environments.

Features and Benefits

- All metal construction
- Suitable for use up to 300°C
- Stays in position whether tightened or not
- Suitable for use in highly corrosive environments
- Reusable



Specifications:

Finish	Plain
Material	Stainless Steel
Stainless Steel Type	316, A4
Thread Size	M5
Type	Aerotight
Thickness	6.02 mm
Thread Pitch	0.8
Width Across Flats	8 mm
Wrenching Height	3.49 mm