



**Part Number :** [732760112](#)  
**Product Description :** 50 Ohms, N Plug, Straight, Crimp Style, LMR-400 Cable, Nickel (Ni) Plated, One Piece Per Bag  
**Series Number :** 73276  
**Status :** Active  
**Product Category :** RF / Coaxial Connectors




## Documents & Resources

**Drawings**  
[732760112\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73276
Description	50 Ohms, N Plug, Straight, Crimp Style, LMR-400 Cable, Nickel (Ni) Plated, One Piece Per Bag
Product Name	N
Style	Cable
Type	Medium
UPC	884982654945

### Electrical

Frequency	11 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 1000 Vrms@Sea Level

### Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	None
Net Weight	43.000/g
Orientation	Straight
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Wire/Cable Type	LMR-400