



The Ultra Portable Slim DVD burner GP57EB40 attracted by its simple design. With only 200 grams, the drive will burn all standard DVD and CD formats and also supports the new M-Disk Media for 1000 years data security. The power is supplied only via the USB interface, making the device even more versatile. The Drive also supports Jamless Play and Silent Play for quiet and smooth playback.

ODD

| | |
|-----------------------------|--|
| Type | Portable Super Multi Drive |
| Data buffer | 0,75 MB |
| Supporting Operating System | Windows 8.1, Windows 8, Windows 7, Windows Vista, Windows XP, Windows server 2008, Windows server 2003, Mac OS X |

Write Speed

| | |
|------------------|---------------------------------|
| DVD-R (SL/DL) | 2x CLV, 4x PCAV, 8x CAV |
| DVD-R DL | 2x CLV, 4x PCAV, 6x PCAV |
| DVD-RW | 2x CLV, 4x, 6x ZCLV |
| DVD-RAM | 2x, 3x CLV, 5x PCAV |
| M-DISC(DVD+R SL) | 4x PCAV |
| DVD+R | 2.4x CLV, 4x PCAV, 8x CAV |
| DVD+R DL | 2.4x CLV, 4x PCAV, 6x PCAV |
| DVD+RW | 2.4x CLV, 4x ZCLV, 8x ZCLV |
| CD-R | 10x CLV, 16x PCAV, 24x CAV |
| CD-RW | 4x, 10x CLV, 16x ZCLV, 24x ZCLV |



Read Speed

| | |
|-------------------|------------------|
| DVD-R/RW/ROM | 8x/8x/8x max. |
| DVD-R DL | 8x max. |
| DVD-RAM (Ver.2.2) | 6x max. |
| DVD-Video | 4x max. |
| M-DISC(DVD+R SL) | 8x CAV |
| DVD+R/+RW | 8x/8x max. |
| DVD+R DL | 8x max. |
| CD-R/RW/ROM | 24x/24x/24x max. |
| CD-DA | 24x max. |

Average access time

| | |
|---------|--------|
| DVD-ROM | 160 ms |
| CD-ROM | 140 ms |

General Features

| | |
|------------------------|---------------------|
| Interface | USB 2.0 |
| Operating Temperature | 5 to 40° C |
| Storage Temperature | -30 to 60 °C |
| Disc Loading | Drawer |
| Dimensions (W x D x H) | 141 x 136.5 x 14 mm |
| Mass | 200g |

Writing Software

| | |
|----------|----------|
| Software | Power2Go |
|----------|----------|

EAN

| | |
|-----|---------------|
| EAN | 8806087132199 |
|-----|---------------|