



PART NO.	MD-3P	MD-4P	MD-5P	MD-6P	MD-7P	MD-8P
POSITION						

P1	STRIPPED JACKET 35mm		
1	TINNED 3mm	BLACK	
2	TINNED 3mm	WHITE	
3	TINNED 3mm	RED	
4	TINNED 3mm	YELLOW	
5	TINNED 3mm	PURPLE	
6	TINNED 3mm	BLUE	
7	TINNED 3mm	GREEN	
8	TINNED 3mm	BROWN	
SHIELD	TINNED 3mm	DRAIN	

\* NOTE: All relevant materials are complied with RoHS directive .

3	MOLDED PVC BLACK		M304
2	NON-UL 3C-8C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, JACKET BLACK,	Lmm	M304
1	MINI DIN 8 MALE, GOLD FLASH ON CONTACTS, BLACK INSULATOR	1	M108
No.	DESCRIPTION	Q'TY	Supplier
APPROVED		Cable Length Unless Other Spec. Tolerances:	
CHECKED	HU	0 ~200mm	±10mm
DRAWING	JUDY	201~1000mm	±20mm
		1001 ~1500mm	±25mm
		1501 ~2100mm	±30mm
		2100mm↑	±40mm
DATE	08/MAY/12	ITEM NO.	UNIT:mm



CHECKED

