



LENOX Diamond™ Reciprocating Saw Blade

10833800RDG



- Nickel alloy-brazed diamond particles maintain sharpness
- Engineered for faster performance up to 3X faster
- Straight clean cuts
- Durable chrome alloy backing steel provides extra stability

The LENOX Diamond™ Reciprocating Saw Blade has been designed to last longer with nickel alloy-brazed particles coating which helps to maintain sharpness. The narrow kerf enables thinner high performance faster cutting up to 3x faster compared to traditional blades. The Diamond recip blade cuts clean and straight cuts unlike bulky snap cutters which crush pipes and leave ragged uneven cuts.

Specifications	
TPI	Single tang Diamond coating
Size	200 x 19 x 1 mm
Blade Quantity	1