

## FEATURES

- **Alloy Steel Construction:** Offers exceptional strength and resistance to bending, ensuring long-lasting performance.
- **1200 mm Overall Length:** Provides superior leverage, making it easier to lift and pry heavy objects.
- **ANSI-ESD S20.20:2021 Compliant:** Meets industry standards for electrostatic discharge, ensuring safe use in sensitive environments.
- **REACH Compliant:** Assures that the product meets European Union regulations for chemical safety.
- **Ergonomic Design:** Enhances user comfort and reduces fatigue during prolonged use.

## RS PRO Alloy Steel Pry Bar, 1200 mm

RS Stock No: 555-903



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO Alloy Steel Pry Bar is a robust tool designed for heavy-duty prying and lifting applications. With its 1200 mm length, it provides excellent leverage, making it ideal for industrial environments where strength and durability are paramount.

### General Specifications

Claw Ended	Yes
Product Type	Pry Bar

### Mechanical Specifications

Material	Alloy Steel
Overall Length	1200 mm

### Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, REACH
---------------------	-----------------------------

