

## DCH274P2T-QW

SDS-plus XR 18V 5Ah Li-Ion 2.1J Rotary Hammer



5035048560037



### Product Description:

Impact Force (E.P.T.A.): 2.1No Load Load (RPM): 0-1100Ø Wood/Concrete/Metal Drilling (mm): 26/24/13Stroke Rate (cps/min): 0-4600Vibration Level (m/s<sup>2</sup>): 6.6Mode (Rotation/Perforation/Impact): 3Quick-Change Chuck

### Product features and benefits:

- Rotation stop for light chiseling work Ideal for drilling holes from 6 to 14 mm in diameter in concrete, brick or various building materials
- Brushless motor - Less friction, therefore 50% less heat, more durability and autonomy LED improving visibility when drilling Drill more than 90 holes (10mm Ø x 80mm) with a battery charge Compact and lightweight, This rotary hammer is ideal for
- 
- 
- pegging.
- Perform & Protect: Lowest vibration level in the class 6.6 m/s<sup>2</sup>, more user comfort 3-jaw keyless chuck with SDS-Plus adapter to allow you to fit your conventional shank drills Electronic clutch for sustained torque and durability Rubber grip and patented gearing for more
- comfort Compact housing for access to all places
- 
- 

### Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

### Included Items:

- Mallette de transport TSTAK (x1)
- Multi-position side handle (x1)
- Batteries 5,0Ah (x2)
- Interchangeable SDS-Plus Tool Holder (x1)
- Chargeur multi voltage (x1)
- 3-jaw 13 mm changeover chuck Quick Hook (x1)
- Hook Belt (x1)

### Specifications techniques :

- Drilling capacity (wood): 26 mm
- Drilling capacity (masonry): 24 mm Capacity
- Battery [Imperial]: 5 Ah Weight (including battery): 3.3 Kg Drilling Capacity (Metal):
- 
- 
- 13 mm Tool Holder [Imperial]
- 
- : SDS- Plus

