


FEATURES

- Insulated hot junction
- Mineral insulation for durability and high performance
- Conforms to IEC standards
- Flexible, can be bent into shape for easy installation
- 310 stainless steel sheath

RS PRO Type K Thermocouple 1m Length, 1mm Diameter → +750°C

RS Stock No.: 787-7778



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS Pro a range of type K thermocouple temperature sensors or probes that conform to IEC standards. These thermocouple temperature probes have a durable construction and feature a 310 stainless steel mineral insulated flexible sheath that can be bent and formed to suit a wide range of applications. The thermocouple has a single element insulated junction for a reduction in electrical interference. One end of the thermocouple is terminated with a miniature flat pin plug for a quick and easy connection

General Specifications

Thermocouple Type	Type K
Temperature Measurement Range	-40°C to 1100°C
Construction	Flexible mineral insulated probe with 310 stainless steel sheath
Measuring Junction	Single element, insulated hot junction from sheath
Application	General purpose, Thermocouple probes include heat exchangers, power stations, brick and cement kilns, heat treatment and annealing furnaces, thermostats, food thermometers, vehicle diagnostics and in laboratories
Temperature Accuracy	IEC 584-2 Class 1

Mechanical Specifications

Probe Diameter	1mm
Probe Length	1m
Probe Body Material	Stainless Steel
Insulation / Sheath Material	Mineral insulation
Termination Type	Miniature Plug

Approvals

Standards Met	IEC
Compliance/Certifications	IEC 584







T/C Type	Conductors	Length	Termination	+Positive tail wire	-Negative tail wire code	Allied Code	RS order Code
'K' 'K'	1/0.2mm 1/0.2mm	1 metre 2 metre	Mini plug Mini plug	Green Green	White White	70643600	363-0250 110-4482
'K'	1/0.2mm	5 metre	Mini plug	Green	White		123-6306
'K'	1/0.2mm	10 metre	Mini plug	Green	White		123-6307
')' ')' ')'	1/0.2mm 1/0.2mm 1/0.2mm 1/0.2mm	1 metre 2 metre 5 metre 10 metre	Mini plug Mini plug Mini plug Mini plug	Black Black Black Black	White White White White	70643599	363-0244 123-6308 123-6309 123-6310
'T' 'T' 'T' 'T'	1/0.2mm 1/0.2mm 1/0.2mm 1/0.2mm	1 metre 2 metre 5 metre 10 metre	Mini plug Mini plug Mini plug Mini plug	Brown Brown Brown Brown	White White White White	70643601	363-0266 123-6311 123-6312 123-6313



T/C Type	Conductors	Cores	Reel Length	Allied code	RS order code
1 1	1/0.2mm 1/0.2mm	+Black/-White +Black/-White	25 metres 50 metres	70657194 70657195	827-5980 827-5984
J K K T	1/0.315mm 1/0.315mm 1/0.315mm 1/0.315mm 1/0.315mm 1/0.315mm	+Black/-White +Black/-White +Green/-White +Green/-White +Brown/-White	25 metres 50 metres 25 metres 50 metres 25 metres 50 metres	70657198 70657199 70657200 70657205 70657208 70657206	827-5993 827-5996 827-6000 827-6019 827-6028 827-6022
J K K	1/0.508mm 1/0.508mm 1/0.508mm 1/0.508mm	+Black/-White +Black/-White +Green/-White +Green/-White	25 metres 50 metres 25 metres 50 metres	70657197 70657201 70657203 70657204	827-5990 827-6003 827-6012 827-6016
J K T N	7/0.2mm 7/0.2mm 7/0.2mm 7/0.2mm	+Black/-White +Green/-White +Brown/-White +Pink/-White	25 metres 25 metres 25 metres 25 metres	70657202 70657207 70657209 70657210	827-6006 827-6025 827-6031 827-6034

	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Exten	ision:					
KX	7/0.2mm	+Green/-White	Green	10 metres	70657084	827-5615
KX	7/0.2mm	+Green/-White	Green	25 metres	70641729	236-3820
KX	7/0.2mm	+Green/-White	Green	50 metres	70657085	827-5619
KX	7/0.2mm	+Green/-White	Green	100 metres	70646156	611-7889
KX	7/0.2mm	+Green/-White	Green	200 metres	70657088	827-5628
	= 10.0				========	
JX	7/0.2mm	+Black/-White	Black	10 metres	70641640	219-4753
JX	7/0.2mm	+Black/-White	Black	25 metres	70657078	827-5592
JX	7/0.2mm	+Black/-White	Black	50 metres	70657079	827-5596
JX	7/0.2mm	+Black/-White	Black	100 metres	70641737	236-3915
JX	7/0.2mm	+Black/-White	Black	200 metres	70657081	827-5606
TX	7/0.2mm	+Brown/-White	Brown	10 metres	70641637	219-4703
TX	7/0.2mm	+Brown/-White	Brown	25 metres	70641734	236-3870
TX	7/0.2mm	+Brown/-White	Brown	50 metres	70657095	827-5653
TX	7/0.2mm	+Brown/-White	Brown	100 metres	70651749	762-1146
TX	7/0.2mm	+Brown/-White	Brown	200 metres	70657098	827-5662
17	7/0.211111	*Browny *Winte	DIOWII	200 metres	70037030	027-3002
NX	7/0.2mm	+Pink/-White	Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-White	Pink	25 metres	70657091	827-5637
NX	7/0.2mm	+Pink/-White	Pink	50 metres	70657089	827-5631
NX	7/0.2mm	+Pink/-White	Pink	100 metres	70657092	827-5640
	-	•				



T/C Type	Conductors	Cores	Reel Length	Allied code	RS order code
KX	1/0.2mm	+Yellow/-Red	25 metres	70656106	814-0030
KX	1/0.2mm	+Yellow/-Red	50 metres	70656111	814-0049
KX	1/0.2mm	+Yellow/-Red	100 metres	70656109	814-0042
KX	7/0.2mm	+Yellow/-Red	25 metres	70656110	814-0046
KX	7/0.2mm	+Yellow/-Red	50 metres	70656113	814-0055
KX	7/0.2mm	+Yellow/-Red	100 metres	70656114	814-0058
KX	1/0.3mm	+Yellow/-Red	25 metres	70656104	814-0024
KX	1/0.3mm	+Yellow/-Red	50 metres	70656107	814-0033
KX	1/0.3mm	+Yellow/-Red	100 metres	70656108	814-0036
TX	1/0.3mm	+Blue/-Red	25 metres	70656121	814-0080
TX	1/0.3mm	+Blue/-Red	50 metres	70656126	814-0099
TX	1/0.3mm	+Blue/-Red	100 metres	70656124	814-0092
TX	1/0.2mm	+Blue/-Red	25 metres	70656125	814-0096
TX	1/0.2mm	+Blue/-Red	50 metres	70656128	814-0106
TX	1/0.2mm	+Blue/-Red	100 metres	70656129	814-0109

T/C Type	Conductors	Cores	Jacket	Reel Length	Allied code	RS order code			
Extension:									
KX	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656102	814-0018			
KX	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656105	814-0027			
KX	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656103	814-0020			
JX	7/0.2mm	+ White/-Red	Black	25 m	70656096	813-9995			
JX	7/0.2mm	+ White/-Red	Black	100 m	70656098	814-0005			
JX	7/0.2mm	+ White/-Red	Black	200 m	70656099	814-0008			
TX	7/0.2mm	+Blue/-Red	Blue	25 m	70656119	814-0074			
TX	7/0.2mm	+Blue/-Red	Blue	100 m	70656122	814-0083			
TX	7/0.2mm	+Blue/-Red	Blue	200 m	70656123	814-0086			
Compensating:									
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656127	814-0103			
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656130	814-0112			
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656131	814-0115			



	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Compensating:						
VX (KCB)	7/0.2mm	+Green/-White	Green	10 metres	70657082	827-5609
VX (KCB)	7/0.2mm	+Green/-White	Green	25 metres	70641629	219-4551
VX (KCB)	7/0.2mm	+Green/-White	Green	50 metres	70657080	827-5603
VX (KCB)	7/0.2mm	+Green/-White	Green	100 metres	70641630	219-4573
VX (KCB)	7/0.2mm	+Green/-White	Green	200 metres	70657083	827-5612
VX (KCB)	13/0.2mm	+Green/-White	Green	10 metres	70657086	827-5621
VX (KCB)	13/0.2mm	+Green/-White	Green	25 metres	70657087	827-5625
VX (KCB)	13/0.2mm	+Green/-White	Green	50 metres	70657090	827-5634
VX (KCB)	13/0.2mm	+Green/-White	Green	100 metres	70651750	762-1152
U (RCA)	7/0.2mm	+Orange/-White	Orange	10 metres	70657096	827-5656
U (RCA)	7/0.2mm	+Orange/-White	Orange	25 metres	70646158	611-7902
U (RCA)	7/0.2mm	+Orange/-White	Orange	50 metres	70657097	827-5659
U (RCA)	13/0.2mm	+Orange/-White	Orange	10 metres	70641641	219-4769
U (RCA)	13/0.2mm	+Orange/-White	Orange	25 metres	70657093	827-5643
U (RCA)	13/0.2mm	+Orange/-White	Orange	50 metres	70657094	827-5647