

FEATURES

- Good flexibility for ease of use
- Resistant to a wide range of chemicals including many acids / alkalis
- Specially selected high tensile polyester fibres
- EC compliant for food contact applications
- Manufactured from cadmium and silicone-free materials

RS PRO PVC Flexible Tubing, Transparent, 13.5mm External Diameter, 25m Long, Reinforced, 29mm Bend Radius, Chemical,

RS Stock No.: 440-054



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Flexible Tubes



Product Description

This RS Pro PVC tubing is perfect to use in a multitude of applications, whether is DIY or commercial use, the EC compliant low toxic hose is reliable and highly durable over time. Suitable for liquids such as water, fuels, oils and other chemicals, this RS Pro hose is also suited for use within the food industry and can be used for air and gas applications. This multi-purpose, high-quality all-round performer is universally popular, especially for the conveyance of air and water.

General Specifications

Material	PVC
Colour	Transparent
Reinforced	Yes
Application	Chemical, Compressed Air, Food, Liquid, Water, Widely used by the caravan industry for piping water and chemicals, Popular for pharmaceutical / scientific applications for the transfer of chemicals, Air applications such as pneumatic tools, For the transfer of food substances and liquids

Mechanical Specifications

Inner Diameter	8mm
Outer Diameter	13.5mm
Length	25m
Bend Radius	29mm
Safety Factor	4:1



Operation Environment Specifications

Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+60°C
Maximum Working Pressure	16bar

Approvals

Compliance/Certifications	BS6066, ISO5774/ RoHS compliant



roduc	t Ref	CR03	CR05	CR06	CR08	CR10	CR12	
x	30m roll	-				1010		
tock	100m roll)						
Nomina	l nize	3.0 x 8mm	5 x 10mm	6.3 x 11.5mm	8 x 13.5mm	10 x 16mm	12.5 x 18.5mm	
nternal	Diameter	3.2 ± 0.20mm	4.75mm ± 0.25	6.3 ± 0.25mm	8.0 ± 0.25mm	10.0 ± 0.25mm	12.5 ± 0.25mm	
xterna	Diameter	8.0 ± 0.25mm	10.0mm ± 0.25	11.5 ± 0.30mm	13.5 ± 0.30mm	16.0a 0.30mm	18.5 ± 0.30mm	
ength '	Tolerance			BS EN I	3O 1307 (± 1%)			
Maximu Pressur	ım Working ə	32 Bar	27 Bar	16 Bar	16 Bar	15 Bar	15 Bar	
Minimur Pressur	m Burat •	128 Bar	108 Bar	64 Bar	64 Bar	60 Bar	60 Bar	
Bend ra	dius	20mm	20mm	28mm	29mm	40mm	55mm	
Warking Temper				- 15	°C to + 60°C			
Material		Flexible PVC						
Materia	Softness	BSS45 FDA Approved						
Flamma	bility	Self Extinguishing						
Weight	per meter	0.056Kg	0.074Kg	0.093Kg	0.123Kg	0.163Kg	0.187Kg	
Coil We	ight	1.68 Kg	2.22Kg	2.78Kg	3.70Kg	4.89Kg	5.61Kg	
Packagi	ing	Strapex Ties and Shrinkwrap						
Applica	ble	BS EN ISO 5774 (Plastic hoses, Textile-reinforced types for compressed-air applications.) & BS EN ISO 6224 (Thermoplastics hoses, textile						
Standar	da	reinforced, for general- purpose water applications)						

Flexible Tubes



Produc	t Ref	CR16	CR19	CR25	CR32	CR38	CR50
Ex	30m roll	••					
Stock	100m roll						
Nomina	l size	16 x 23mm	19 x 26mm	25 x 33mm	32 x 42mm	38 x 48mm	50 x 62mm
Internal	Diameter	16.0 ± 0.25mm	19.0 ± 0.25mm	25.0 ± 0.50mm	32.0 ± 0.50mm	38.0 ± 0.50mm	50.0 ± 0.75mm
Externa	l Diameter	23.0 ± 0.50mm	25.75 ± 0.50mm	32.50 ± 0.50mm	42.0 ± 0.75mm	48.0 ± 1.00mm	62.0 ± 1.00mm
	Tolerance						
Maximu Pressur	ım Working ə	12 Bar	10 Bar	10 Bar	10 Bar	10 Bar	8 Bar
Minimu Pressur	m Burst e	48 Bar	40 Bar	40 Bar	40 Bar	40 Bar	32 Bar
Bend ro	dius	95mm	135mm	210mm	320mm	420mm	650mm
Norking Temper							
Materia							
Mary Street	Softness						
lamma				Tak Your below			1.0000000000
	per meter	0.289Kg	0.310Kg	0.432Kg	0.684Kg	0.684Kg	1.476Kg
Coil We		8.00Kg	9.30Kg	12.96Kg	20.52Kg	20.52Kg	44.29
Packag							
Applica							
Standar	ds .						