

Technical data sheet

Article number:
924-00509

BLU2.5

Product Group	Un-Insulated Bootlace Ferrules
Product Family	Bootlace Terminals
Material	Copper (CU)
Colour	Silver-matt (MTSR)
Application Range	Low Voltage
Conductor Size (mm ²)	2.5 mm ²
Diameter (D)	3.4 mm
Length (L)	8 mm
Length (L2)	7 mm
Max Voltage	600 V
Operating Temperature	-55 °C to +155 °C
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
Ø (D2)	2.3 mm
ROHS compliant	Yes

