



Datasheet

RS PRO CERAMIC CAPACITOR - CLASS II Hi-K TYPE

Stock number: 180-4840, 1805127

EN



Features and Benefits

- Capacitance has non-linear temperature coefficient.
- Large capacitance in small size.
- Epoxy Coating for 1KV, 2KV and 3KV parts (equivalent to UL94V-0 standards).
- RoHS Compliance.
- Halogen free products are available.
- Wide range of general purposes applications.

rspro.com



General specification

Capacitance Range	470pF
Capacitance Tolerance	10%
Operating Temperature Range	-25°C ~ +85°C
Rated Voltage	3000 VDC
Dielectric Code	Y5P
Diameter Max	9.0 mm
Packing/Pitch/Lead Length	Ammo Box & Pitch 15.0mm
Lead Spacing	7.5.0 +/-1 mm
Coating	Epoxy Resin /Halogen Free and Pb Free