

## Portable Touchscreen Monitors 4K



**Part Number:** 32238, 32239

### Description

- Available in two size: 15.6" & 17.3"
- Panel: Capacitive Touch Panel, IPS Technology
- Panel type: 10-point multi-touch with G+FF technology
- Resolution (H x V): 3840 x 2160px
- Aspect ratio: 16:9
- View angles LR,UD (CR>10): H 178° / V 178° (Min)
- Display colours: 16.7M colours
- Input 1: USB-C x 2 (Full-featured USB-C)
- Input 2: Standard HDMI (1.4) x 1
- Output: USB-A 2.0 x 1
- Output: 3.5 mm Audio jack
- Supports: HDR, FreeSync, Low Blue Light
- Stand: Built-in kickstand, Tilt: from 0° up to 85°
- Frame material: Aluminium
- 2-year limited warranty



October 2023

## Portable Touchscreen Monitors 4K



**Part Number: 32238, 32239**



### Languages

Front of pack: English (Product description also in French)

Back of pack: English, French, German, Dutch, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Serbian, Croatian, Traditional Chinese, Simplified Chinese & Korean

### Quick Installation Languages:

English, French, German, Dutch, Italian, Spanish, Portuguese, Polish, Russian, Czech, Hungarian, Serbian, Croatian, Traditional Chinese, Simplified Chinese, & Korean

### Pack Contents:

- Verbatim Touchscreen Monitor 4K
- 2x USB-C to USB-C cable 1.0m
- HDMI-HDMI cable 1.5m
- EU power supply with UK adapter (PD up to 20W)
- Neoprene protection sleeve
- Quick start guide

## Portable Touchscreen Monitors 4K



## Logistic Information

| Reorder No. | Description                                                            | Barcode       | EAN-128                                                            | EAN-14                           |
|-------------|------------------------------------------------------------------------|---------------|--------------------------------------------------------------------|----------------------------------|
| 32238       | Verbatim PMT-15-4K Portable Touchscreen Monitor 15.6" 4K Metal Housing | 0023942322382 | (02)00023942322382(37)02(91)491<br>(02)00023942322382(37)06(91)491 | 20023942322386<br>50023942322387 |
| 32239       | Verbatim PMT-17-4K Portable Touchscreen Monitor 17.3" 4K Metal Housing | 0023942322399 | (02)00023942322399(37)02(91)491<br>(02)00023942322399(37)04(91)491 | 20023942322393<br>50023942322394 |

| Reorder No.                    | 32238                                                   | 32239               |
|--------------------------------|---------------------------------------------------------|---------------------|
| Pack dimensions LxWxH          | 280 x 466 x 58 mm                                       | 311 x 522 x 57.5 mm |
| Pack weight                    | 2 540 g                                                 | 3 180 g             |
| Pcs per pack                   | 1                                                       | 1                   |
| Inner cartons dimensions LxWxH | 482 x 132 x 300 mm                                      | 500 x 132 x 320 mm  |
| Inner cartons weight           | 5 480 g                                                 | 6 760               |
| Pack per Inner Carton          | 2                                                       | 2                   |
| Outer cartons dimensions LxWxH | 500 x 430 x 330 mm                                      | 556 x 285 x 338 mm  |
| Outer cartons weight           | 17 340 g                                                | 14 500 g            |
| Pcs per outer carton           | 6                                                       | 4                   |
| Outer cartons per layer        | 4 Layers x 4 Outer Cartons + 3 Layers x 2 Outer Cartons | 6                   |
| Layers per pallet              | 7 (4+3)                                                 | 4                   |
| Outer Cartons per pallet       | 22                                                      | 24                  |
| Pcs per pallet                 | 132                                                     | 96                  |