



Main

Product brand	Schneider Electric
Range	Odace
Type number	NH3508
Product or component type	Connected shutter control
Concentrator compatibility	Wiser hub generation 2
Mobile App name	Wiser Home

Complementary

Device application	Blind actuator
Device presentation	Mechanism with fixing frame
Technology type	Electronic
Number of rocker	1
Actuator	Push-button
Device mounting	Wall mounted Surface
Fixing mode	Adhesive tape By screw
Switch function	Jalusi Push-button
Switch application	Blind control
Load type	Motor (single-phase): 500 VA at 230 V 50 Hz AC (indoor)
Function available	Blind control
[Ue] rated operational voltage	230 V AC 50 Hz
Rated current	4 A
Standby consumption	0.5 W
Associated fuse rating	10 A
Colour tint	White (RAL 9003)
Surface finish	Glossy
Surface treatment	Polished
Material	Thermoplastic: cover plate PC (polycarbonate) GF10 FR: casing
Kit composition	3 x push-button switch Mounting box
Local signalling	Commissioning: 3 1 dual colour LED (green/red)
Signalling function	Commissioning
Total number of wires	4
Pilot light	Green and red ON indicator
Number of outputs	1
Control type	Remote control by auxiliary double push-button blind control
Maximum number of connected devices	Zigbee: 3
Communication network type	Wireless Zigbee (2.4 GHz), 10 mW at < 50 m
Connected auxiliaries	Maximum 10 auxiliary push-buttons, distance : 10...50 m

Provided equipment	Adhesive tape Battery Mounting box
Wiring configuration	3 wires with neutral
Connections - terminals	Screw type terminals
Clamping connection capacity	1.5...2.5 mm² for solid stranded cable(s)
Shape of screw head	Pozidriv No 1
Tightening torque	0.5 N.m
Type of installation	Indoor installation
Quantity per set	5 pieces
Type of packing	Carton
Ambient air temperature for operation	5...40 °C
Ambient air temperature for storage	5...40 °C
IP degree of protection	IP20 local/remote
IK degree of protection	IK02
Embedding depth	29 mm
Depth	41 mm
Width	85 mm
Height	85 mm
Net weight	0.1 kg
Standards	EN 60730-2-7 EN 60669-2-1 EN 301 489-17
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Product certifications	CE[RETURN]NF[RETURN]VDE
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information