



All AMPOWER Lug Crimp Terminal, Long Barrel (0)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 46754-2
HYP8 AMPOWER 400MCM DIE SET




TE Part # 69653
HYP8 AMPOWER 350MCM 69082 DIE SET

Customers Also Bought



TE Part #3-520408-2
ULTRA-FAST 250 ASY REC 16-14 AWG TPBR



TE Part #327290
TERMINAL,AMPOWER 600MCM 1/2




TE Part #206837-1
CPC PLUG ASSEMBLY SIZE 23-24



TE Part #325805-1
AMPOWER TERM.300 MCM.1/2,STD.



TE Part #30928
TERMINAL,DG R 16-14 10



TE Part #326808
TERMINAL,AMPOWER 500MCM 3/8



TE Part #2-33460-2
TERMINAL,SOLIS R 8 10



TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals

Documents

Product Drawings

TERMINAL,AMPOWER 400MCM 0

English

CAD Files

Customer View Model

ENG_CVM_CVM_326021_M.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_326021_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_326021_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages
AMPOWER Terminals and Splices Flyer
English

Product Specifications
Application Specification
English

Instruction Sheets
Instruction Sheet (U.S.)
English
Instruction Sheet (U.S.)
English

Agency Approvals
UL Report
English