

## FEATURES

- **2 m cable length:** Provides flexibility and reach for various setups
- **IEC C19 to IEC C20 connectors:** Ensures compatibility with a wide range of equipment
- **16 A current rating:** Suitable for high-power applications
- **250 V voltage rating:** Supports standard voltage requirements
- **Black PVC jacket:** Durable and resistant to wear and tear
- **Straight plug and socket:** Simplifies installation and connection

## RS PRO 2 m Power Cable, IEC C19 to IEC C20

RS Stock No: 558-933



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO power cable is designed for reliable and efficient power transmission in industrial and commercial environments. With a length of 2 metres, it facilitates easy connection between devices with IEC C19 and IEC C20 connectors, supporting a current rating of 16 A and a voltage of 250 V.

## General Specifications

Connector Type A	IEC C19
Connector Type B	IEC C20
Jacket Colour	Black
Mains Socket Type	Straight
Product Type	Power Cable

## Mechanical Specifications

Cable Length	2 m
Jacket Material	Polyvinyl Chloride

## Electrical Specifications

Current Rating	16 A
Mains Plug Type	Straight
Voltage	250 V

## Approvals

Standards/Approvals	CCCs, CSA, EAC, ENEC 11, ICC, JET, PSE, R31947, RCM N10544, UL
---------------------	--

