

Han High Temp 10B Base Panel 2 levers



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 810 0391
Specification	Han High Temp 10B Base Panel 2 levers
HARTING eCatalogue	https://harting.com/09628100391

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® High Temp
Type of hood/housing	Bulkhead mounted housing
Type	Low construction

Version

Size	10 B
Locking type	Double locking lever

Technical characteristics

Tightening torque	1 Nm Fixing screws M4
Limiting temperature	-40 ... +200 °C With Han® High Temp components
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	FPM
Colour (seal)	Red
Material (locking)	Stainless steel
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Commercial data

Packaging size	1
Net weight	1 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140073982
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466