

PRC 20/3-C1-FT25-MS2,5 - Device connector front mounting



1313299

<https://www.phoenixcontact.com/gb/products/1313299>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Range of articles: PRC 20, color: black, number of positions: 3, min. conductor cross section: 0.5 mm², max. conductor cross section: 2.5 mm², rated voltage: 400 V, rated current: 25 A, Connection method: Screw connection, Contact connection type: Pin, Setting option for release: 1. with a tool or 2. by hand, scope: AC

Your advantages

- More space on the device front with current transmission up to 20 A in a minimum amount of space
- Duo-Unlock technology for greater flexibility during installation and maintenance
- Reliable use under extreme ambient conditions with high degrees of protection and impact resistance
- Simple handling with proven crimp or screw connection technology
- Mechanical and color coding for quick and error-free startup

Commercial data

Item number	1313299
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABLHAD
Product key	ABLHAD
GTIN	4063151568542
Weight per piece (including packing)	40.3 g
Weight per piece (excluding packing)	28.431 g
Customs tariff number	85366990
Country of origin	PL

PRC 20/3-C1-FT25-MS2,5 - Device connector front mounting



1313299

<https://www.phoenixcontact.com/gb/products/1313299>

Technical data

Notes

Order information:	Setting option for release: 1. with a tool or 2. by hand
Note on application	For assembly notes, please refer to the packing slip


Product properties

Product type	Panel feed-through
Product family	PRC 20
Area of application	AC
Number of positions	3
Connection profile	2+PE
Coding	3-C1

Insulation characteristics

Protection class	II
------------------	----

Dimensions

Dimensional drawing	
Width	34 mm
Height	38.4 mm
Length	53.7 mm

Electrical properties

Nominal voltage ATD	400 V (III/2.00) in accordance with IEC 61984
	400 V AC (III/2.00) in accordance with IEC 61535
	600 V AC / DC (III/2.00) in accordance with UL 2238 / UL 2237
	500 V DC (III/2.00) in accordance with IEC 61535
Rated current	25 A (With 2.5 mm ² conductor cross section in accordance with IEC 61984)

Material specifications

Color (Housing)	black (RAL 9005)
Material Housing	PPE
Material Contact carrier	PPE
Material Contact	CuZn (Contact material, Pb < 0.1)
Material	PPE (Nut)
Material Seal	EPDM (Cable seal)

PRC 20/3-C1-FT25-MS2,5 - Device connector front mounting



1313299

<https://www.phoenixcontact.com/gb/products/1313299>

	EPDM (Flat gasket)
Flammability rating according to UL 94	V0

Cable/line

Single wire, cross section	0.5 mm ² 2.5 mm ²
Stripping length of the individual wire	10 mm
Halogen-free	yes

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP68 (2 m / 2 h)
	IP69
Category of shock impact	IK08 (-25°C)
Ambient temperature (operation)	-40 °C ... 85 °C (observe derating)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 85 °C


PRC 20/3-C1-FT25-MS2,5 - Device connector front mounting

1313299

<https://www.phoenixcontact.com/gb/products/1313299>

Drawings

Dimensional drawing




PRC 20/3-C1-FT25-MS2,5 - Device connector front mounting




1313299

<https://www.phoenixcontact.com/gb/products/1313299>



Derating



Derating

PRC 20/3-C1-FT25-MS2,5 - Device connector front mounting



1313299

<https://www.phoenixcontact.com/gb/products/1313299>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1313299>

	 UL Listed Approval ID: E221474-20240312			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	600 V	20 A	-	20 - 14

	 cUL Listed Approval ID: E221474-20240312			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	600 V	20 A	20 - 14	-

	 VDE Zeichengenehmigung Approval ID: 326017-TL3-1			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	500 V	20 A	-	0.5 - 2.5

PRC 20/3-C1-FT25-MS2,5 - Device connector front mounting



1313299
<https://www.phoenixcontact.com/gb/products/1313299>

Classifications

ECLASS

ECLASS-13.0	27440602
-------------	----------

ETIM

ETIM 9.0	EC002566
----------	----------

PRC 20/3-C1-FT25-MS2,5 - Device connector front mounting



1313299

<https://www.phoenixcontact.com/gb/products/1313299>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk