1928DAL Reversible impact wrench

CE 3/4"

- Double hammer impulse device
- 6" long anvil
- Sturdy and compact; high torque
- Reversible lever
- Three power adjustable positions
- Exhaust through handle
- Slip-proof ergonomic handle



6" long anvil

Free speed	**5,000 rpm**
Max. torque	1.695 Nm
Bolt capacity	**CI 8.8 M27⬢41 mm**
Bolt capacity	CI 12.9 M24⬢36 mm
Air inlet	**3/8" GAS**
Working pressure	6,2 bar
Internal hose size (Ø)	**10 mm**
Mean air consumption	240 l/min
Weight	**4,8 kg**



	art.		■ "	kg
019280023	1928DAL	1928 DAL-reversible impact wrench	3/4	4,8