

7611 // MOTION TEX PLUS

Trousers



Elastic waist with raised back
Durable triple-stitched seams
Practical and useful extras



7611 // MOTION TEX PLUS



Shell fabric:	Polyester / cotton, royal blue / black
Lining:	-
Size(s):	24-29, 42-68, 90-110
Packaging unit:	10 piece(s)
Certification:	OEKO-TEX STANDARD 100®

NITRAS MOTION TEX PLUS, long work trousers, royal blue / black (colour code: 2010), 280 g/sqm, breathable material, high wearing comfort, elastic waist with raised back, reinforcement on back belt loop and reinforcements made of Canvas on back, knee, leg pockets and ankles, durable triple-stitched seams, covered button for product protection (e.g. scratches), reflective elements for better visibility, practical and useful extras: thigh pockets with flaps, ruler pocket with additional pocket, knee pockets for protectors with insertion from above, hammer loop, D-ring, OEKO-TEX STANDARD 100®, Comfort Fit, knee protectors 76K (EN 14404) optionally available



Industries

-  Automotive manufacturing
-  Commissioning / shipping

Advantages

- + Elastic waist with raised back
- + Durable triple-stitched seams
- + Practical and useful extras



Further images



Colour variants



7611 // MOTION TEX PLUS
Colour code: 2010



7610 // MOTION TEX PLUS
Colour code: 1000



7612 // MOTION TEX PLUS
Colour code: 1210



7613 // MOTION TEX PLUS
Colour code: 1112



7614 // MOTION TEX PLUS
Colour code: 3010




7616 // MOTION TEX PLUS
Colour code: 2110



7617 // MOTION TEX PLUS
Colour code: 5010

Additional information

	Material	Colour	Grammage
Shell fabric	65% Polyester 35% Cotton	royal blue / black	280 g/qm



Wash separately or with similar colours. Close all zippers before washing and wash inside out. Applies only to non refined products. Do not use fabric softener. Think sustainably and wash at 30° C.

Logistics data

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
24	4059904113046	4059904111844	0,57 m	0,35 m	0,24 m	8,67 kg	20
25	4059904113053	4059904111851	0,56 m	0,35 m	0,22 m	10,7 kg	20
26	4059904113060	4059904111868	0,56 m	0,35 m	0,23 m	10,99 kg	32
27	4059904113077	4059904111875	0,57 m	0,36 m	0,26 m	11,23 kg	20
28	4059904113084	4059904111882	0,58 m	0,35 m	0,26 m	11,56 kg	24
29	4059904113091	4059904111899	0,58 m	0,35 m	0,26 m	11,87 kg	20
42	4059904076952	4059904076969	0,57 m	0,35 m	0,24 m	8,67 kg	32
44	4059904076976	4059904076983	0,57 m	0,35 m	0,23 m	9,08 kg	24
46	4059904076990	4059904077003	0,56 m	0,34 m	0,24 m	9,16 kg	24
48	4059904077010	4059904077027	0,56 m	0,35 m	0,23 m	9,41 kg	24
50	4059904077034	4059904077041	0,56 m	0,35 m	0,24 m	9,78 kg	24
52	4059904077058	4059904077065	0,56 m	0,35 m	0,25 m	10,05 kg	24
54	4059904077072	4059904077089	0,56 m	0,34 m	0,24 m	10,39 kg	24
56	4059904077096	4059904077102	0,56 m	0,35 m	0,23 m	10,64 kg	24
58	4059904077119	4059904077126	0,56 m	0,36 m	0,27 m	10,84 kg	20
60	4059904077133	4059904077140	0,56 m	0,36 m	0,26 m	11,08 kg	24
62	4059904077157	4059904077164	0,57 m	0,35 m	0,26 m	11,32 kg	20
64	4059904077171	4059904077188	0,57 m	0,35 m	0,26 m	11,85 kg	20
66	4059904077195	4059904077201	0,57 m	0,35 m	0,26 m	11,66 kg	20
68	4059904077218	4059904077225	0,56 m	0,35 m	0,26 m	12,38 kg	20
90	4059904113107	4059904111905	0,56 m	0,36 m	0,23 m	10,37 kg	24
94	4059904113114	4059904111912	0,55 m	0,35 m	0,23 m	10,59 kg	20
98	4059904113121	4059904111929	0,57 m	0,35 m	0,23 m	10,98 kg	24
102	4059904113138	4059904111936	0,57 m	0,36 m	0,26 m	11,35 kg	24
106	4059904113145	4059904111943	0,56 m	0,36 m	0,26 m	11,72 kg	24
110	4059904113152	4059904111950	0,56 m	0,35 m	0,26 m	12 kg	20

Customs tariff number: 62034311000
Country of origin: India