




NOTES :

1. MATERIAL:
HOUSING: HIGH TEMPERATURE THERMO PLASTIC.
PIN: COPPER ALLOY.
SOLDER NAIL: SUS.
2. FINISH:
PIN: TIN PLATING OVER NICKEL PLATING OVERALL.
SOLDER NAIL: TIN PLATING OVER NICKEL PLATING OVERALL.
3. PACKAGED IN TAPE AND REEL INSIDE OF CARTON.



1-2834682-0	1-2834684-0	10	25.45
2834682-6	2834684-6	6	18.25
2834682-2	2834684-2	2	11.05
BLACK COLOR,Y KEY	NATURAL COLOR,Y KEY	Position	Dimension A



RECOMMEND PCB LAYOUT
TOLERANCE: $\pm 0.05\text{mm}$

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 23JAN2024		 TE Connectivity	
		E-TRANK_FAN			
		CHW 23JAN2024		NAME DYNAMIC ULTRA 1.80MM PITCH SMT TYPE	
		GEORGE_FU			
		APVD 23JAN2024			
		MING_SHI			
		PRODUCT SPEC			
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE CAGE CODE DRAWING NO RESTRICTED TO A 00779 C=C2834659 -	
		0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ± ±		APPLICATION SPEC 108-137690 114-137708	
		MATERIAL FINISH - - - -		WEIGHT - CUSTOMER DRAWING	
				SCALE 5:1 SHEET 1 OF 1 REV A3	