

Drive shaft adapter EAMB-18-9-8X16-10X12

Part number: 558035

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting diameter 1	8 mm
Mounting diameter 2	10 mm
Size	70
Nominal length	16 mm
Mounting position	optional
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	0.838 kgmm ²
Transmittable torque	12 Nm
Product weight	29 g
Note on materials	RoHS-compliant