



## Dual Handle Paddle Mixer

DWD241-QS

Powerful 1800W motor handles thicker, more viscous materials

3 speed dial for Optimized control and performance

Variable speed trigger for additional control

Dual handle design for complete control and comfort for prolonged mixing

Standard M14 paddle connection for user preferred paddle



Sound Power	96 dB(A)
-------------	----------

Sound Pressure Uncertainty	3 dB(A)
----------------------------	---------

Sound Pressure	85 dB(A)
----------------	----------

Uncertainty K 1 (Vibration)	1.5 m/s <sup>2</sup>
-----------------------------	----------------------

Power Source	Corded
--------------	--------

No Load Speed	225-400/550/725 Rpm
---------------	---------------------