

## CUSTOMER DATA SHEET

Product:	<b>WYPALL® L20 Wipers - Large Roll /Blue</b>	Status:	<b>AUTHORISED</b>
CS No:	<b>07200000</b>	Date:	<b>12.11.02</b>
		Replaces:	<b>New</b>

## PRODUCT DESCRIPTION

WYPALL® L20 Blue Wiper, 1 Ply

## BASESHEET

Fibre Composition		Typical Values
Recycled Fibre	%	Upto 95 % maximum – including 10% internally generated waste
Virgin Fibre	%	15% maximum
Broke - internally generated waste	%	10%
Bleaching Method		Elemental Chlorine-free
Sterilisation		N/A
Ash Content		<2%
Embossing	Yes/No	No

## FINISHED PRODUCT

Property		Typical Values
Format	Folded/Roll	Roll
Basis Weight/No Plies	g/m <sup>2</sup> /No Plies	35/1
Thickness	mm	NM
Water Absorbency Capacity	%	350-550
Water Absorbency Rate	sec	5-9
Oil Absorbency Capacity	%	300-500
Oil Absorbency Rate	sec	45-80
Machine Direction Tensile	N/m/ 1 ply	395
Cross Direction Tensile	N/m/ 1 ply	330
Wet Cross Direction Tensile	N/m/ 1 ply	85
Brightness	%	Blue
Sheet Count	sheets	1000
Sheet Length	mm	380
Sheet Width	mm	235
Roll Diameter	mm	320

## PALLETISATION

Unit of Sale		1 Polywrapped Roll			
Case Dimensions	L x W x H	32 x 32 x 23.5 cm			
Nett Weight/Case	Kg	3.12Kg			
Max Weight/Case	Kg	4.5 Kg			
Pallet Type		Euro	0.5 Euro	GKN	0.5 GKN
No Case/Roll per Pallet		42	30	N/A	45
No Cases per Layer		6	6	N/A	9
No Layers per Pallet		7	5	N/A	5
Type of Packaging - poly/paper - sack/corrugate		Polywrap			
Dispenser Codes		6155 / 6147			

## ADDITIONAL INFORMATION

Quality Accreditation - ISO 9002; BGVV 36<sup>th</sup> Recommendation (applied for)

## NOTE

This data was generated from samples which were taken to be typical of standard product. The data is given for information only. Additional information can be supplied on request.

## CONFIDENTIALITY STATEMENT

These specifications and the confidential information contained herein are the property of Kimberly - Clark. Copies of this material are the property of Kimberly - Clark and should be made only if absolutely necessary. Copies, like the originals are considered as trade secrets.