



PACKING 	INNER 	MASTER 
Display 12 pces	12	48



TECHNICAL DATA

Power supply	DRY BATTERIES
How many batteries are used	3
Battery type	LR1130
Stack technology	ALCALINE
Batteries provided	(INCLUDED)
Battery/battery weight (kg)	0.006
Maximum autonomy (h)	0.5
LED quantity	3
Lighting source	STANDARD LED
Lumen	10
Light beam	DIFFUSE
Switch	YES
Sold in display	12 PCES
Country of origin	CHINA
Material	PLASTIC - ABS
Warranty	2 YEARS
Width (mm)	100
Depth (mm)	50
Height (mm)	28
Net weight (Kg)	0.068

DESCRIPTION

It works...without batteries! The flashlight turns on with a repeated press of your hand, which builds up enough energy to function. You'll never have to recharge it with a cable or batteries! Up to 30 minutes of non-stop brightness: Our flashlight is perfect for camping, hiking, low-light walking, repairs and more. Self-charging: Simply press the handle to charge. No cables, chargers, or batteries required. This flashlight features 3 bright white LED bulbs that illuminate up to 5 meters away. The dynamo flashlight is really useful during power outages, car breakdowns, outdoor activities.... or for kids who want to go on adventures!

LOGISTICS DATA

Packing type	Display 12 pces
Packed product weight (kg)	0.071
Inner width (cm)	25
Inner length (cm)	23
Inner height (cm)	13
Quantity in inner	12
Gross weight inner (kg)	0.970

LOGISTICS DATA

ITF INNER	18003910108377
Master length (cm)	48
Master width (cm)	25
Master height (cm)	27
Quantity in master	48
Master gross weight (kg)	4.300
ITF MASTER	28003910108374
How many pieces on 80x120 pallet (pz)	1440
INTRASTAT Code	85131000
DEEE	0.02
ECOLOGIC SCALES 2025	MLUMI010000
Country of origin	CHINA

