

# Eaton 163835

Catalog Number: 163835

PIFT0H300. Fuse switch disconnecter, 3p, NH00, AC23

General specifications



Product Name	Catalog Number
Eaton Distribution parts	163835
EAN	Product Length/Depth
4015081603657	590 mm
Product Height	Product Width
49.5 mm	280 mm
Product Weight	Compliances
4.319 kg	RoHS conform

## Product specifications

### Features

Motor drive optional

### Fitted with:

Connectors

Error protection

Rated operational power at AC-23A, 400 V, 50 Hz

0 kW

Rated permanent current (Iu)

160 A

Rated uninterrupted current (Iu)

160 A

Conditioned rated short-circuit current Iq

100 kA

Number of poles

Three-pole

Rated operation power at AC-23, 400 V

0 kW

Rated short-time withstand current (Icw)

0 kA

Electrical connection type of main circuit

Screw connection

Actuator position

Front side

Actuator type

Long turning handle

Suitable for

Front mounting

Rated conditional short-circuit current (Iq)

100 kA

Suitable for fuses

NH00

Cable entry type

Side

Degree of protection (front side)

IP40

## Resources

Declarations of conformity

[03\\_pift1\\_110717.pdf](#)

[DA-DC-03\\_PIFT0](#)

Installation instructions

[IL1470403ZU](#)

Power rating at AC-23, 400 V

0 kW

Rated operating voltage (Ue) at AC - max

690 V



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia