

## DWE4217-QS

Meuleuse 125 mm 1200W

5035048464557

**DEWALT**



### Product Description:

Disc Ø (mm): 125Power: 1200W No-load Temperature (RPM): 0-11000Spindle Thread: M14Vibration Level (m/s<sup>2</sup>): 6.2Switch: Slide

### Product features and benefits:

- Soft start provides more safety and control to the user Self-stirring brushes for longer motor life Shaft locking system located on the side, allows working in tight spaces Rubberized handles for a better grip Gearbox with low profile so that you can work in limited spaces New disc clamping system, prevents blockage
- Inductor with connecting wires directly from the winding, for better tool life Dust ejection system, removes the majority of debris,
- 
- 
- 
- protects the motor from dust particles Protected engine from dust
- particle abrasion, for Longer life An even stronger motor to meet the most demanding
- applications Protective guard can be adjusted quickly, without tools The anti-restart system prevents the machine from accidentally restarting after a power
- failure The switch must be returned to the initial position before the engine can be restarted

### Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

### Included Items:

- Tool-free guard (x1)
- Indoor/Outdoor Flange (x1)
- Service Key (x1)
- Multi-position side handle (x1)

### Specifications techniques :

- Power supply: 1200
- In
- Diameter: 125 mm
  - Disc diameter: 125 mm

