

ACTIVARMR™

27-806

Heavy duty supported nitrile finish

Previously known as: Nitratough™ N660



Oil



Heavy Duty

Heavy-duty supported nitrile gloves, offering superb abrasion, grease and oil resistance

- **Advanced defenses:** ActivArm® 27-806 abrasion-resistant gloves feature a fully dipped nitrile coating that covers the fingers and knuckles, offering an excellent barrier against oil as well as grease, and does not degrade like leather or cotton
- **Elevated comfort:** These nitrile gloves are composed of a 100% cotton interlock fleece liner, providing elevated comfort
- **Added protection:** ActivArm® 27-806 hand protection gloves are also stronger and more flexible than PVC, affording superior abrasion resistance

Industries

- Automotive
- Metal fabrication

Applications

- Press shop operations
- Handling structural and body components
- Handling materials with sharp or rough edges

ACTIVARMR™

27-806

Heavy duty supported nitrile finish

Previously known as: Nitratough™ N660

Key Features

- **Fully dipped nitrile coating:** Excellent barrier against oil and grease
- **100% cotton fleece liner:** Optimal wearer comfort assured
- **Abrasion-resistant:** Safety gloves with improved durability

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4221B



4419CIT

Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 27-806	Finishing: Fully Coated Coating Material: Nitrile Liner Material: Cotton Cuff Style: Safety Cuff	8, 9, 10, 11	260-290 mm/10.2-11.4 Inches	Blue	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell