

### General

<b>Carton contents</b>	PT-E300VP labelling machine 18mm strong adhesive black on yellow 8m tape cassette Li-ion rechargeable battery AC adaptor Wrist strap Documentation Carry case
<b>Language support</b>	English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finnish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Turkish, Brazilian Portuguese

### Dimensions & Weights

<b>Without carton</b>	133(w) x 220(d) x 74(h)   740g
<b>With carton</b>	391(w) x 331(d) x 128(h)   2.89kg
<b>Master carton</b>	408(w) x 403(d) x 377(h)   10.01kg
<b>Products per master carton</b>	3

### Built In Features

<b>Keyboard</b>	64 Key Rubber QWERTY/QWERTZ/AZERTY
<b>Dedicated number keypad</b>	Yes
<b>Display type</b>	Backlit Graphic Monochrome LCD with label preview capability
<b>Display resolution</b>	15 characters by 3 lines   128 x 56 dots
<b>Printing speed</b>	20mm/second
<b>Print resolution</b>	180dpi
<b>Maximum print height</b>	15.8mm
<b>Cutter type</b>	Manual full cutter (with cut/pause feature) (fluorine-coated to cut strong adhesive tapes)
<b>Label length</b>	25mm minimum   300mm maximum
<b>Maximum lines per label</b>	5 (for 18mm wide tape)
<b>Tape margins</b>	Large Margin, Small Margin, Chain, No Cut
<b>Vertical text printing</b>	Yes
<b>Mirror printing</b>	No
<b>Copies</b>	1 to 50
<b>Automatic numbering</b>	Count 1 to 50   Incremented by 1 to 9   Numeric and Alphanumeric   Standard, Simultaneous or Advanced

### Label Creation

<b>Smart label application keys</b>	General/Faceplate Cable Wrap/Heat Shrink Tube/ <sup>1</sup> Self-laminated /Cable Flag, Patch Panel / Punch Down Block
<b>Fonts</b>	7   Helsinki, Brussels, Los Angels, Atlanta, Adams, Sofia, Letter Gothic
<b>Font styles</b>	9 (excl. Normal)   Normal, Bold, Outline, Shadow, Solid, Italic, Italic Bold, Italic Outline, Italic Shadow, Italic Solid
<b>Font sizes</b>	6, 9, 12, 18, 24, 36, 42 point
<b>Symbols</b>	384
<b>Frames</b>	7
<b>Barcodes</b>	9   CODE39, ITF 2/5, EAN13, EAN8, UPC-A, UPC-E, CODABAR, GS1-128 (UCC/EAN128), CODE128

### Memory

<b>Max. characters per label</b>	200
<b>Label memory locations</b>	50 (or up to 2,400 characters)

### Supplies

<b>Tape type</b>	TZe, HGe, HSe (Heat Shrink Tube), <sup>1</sup> Self-laminated
<b>Tape widths</b>	3.5, 6, 9, 12 and 18mm

### Optional Accessories

<b>Batteries</b>	BA-E001 Li-ion rechargeable battery AA alkaline/rechargeable batteries (LR6/HR6)
<b>AC adaptor</b>	AD-E001

<sup>1</sup> From 2014. May require firmware update.