



3M™ Adhesive Sealants

Durable, Flexible Bonding & Sealing



550 FC

- Industrial Grade
- Faster Curing
- High Strength



550 FC / AC63

- Accelerated Cure
- AC63 Accelerator



590

- Window Bonding
- P591 Universal Primer



4200 FC

- Marine Grade
- Above/Below Waterline Use
- Fast Cure



5200 / 5200 FC

- Marine Grade
- Above/Below Waterline Use
- Permanent Bond

Polyurethanes

- High strength
- High elongation
- Paintable

HIGH PERFORMANCE SEALING

HIGH PERFORMANCE BONDING

PU All Purpose

540



560



Softer

Sealing

Bonding

Firmer

740 UV



SMP

High Performance

760 UV



Silane Modified Polymers

- Excellent UV resistance
- Primerless bonding
- Isocyanate-free
- Paintable when wet



3000 UV

- Marine Grade
- Above/Below Waterline Use



4000 UV

- Marine Grade
- Above/Below Waterline Use
- Higher Strength & Elongation

MARINE COSMETIC SEALING

MARINE COSMETIC BONDING

Warranty and Limited Remedy: 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES OR CONDITIONS, INCLUDING ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If the 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

3M Industrial Adhesives & Tapes Division
 3M Center, Building 225-35-06, St. Paul, MN 55144-1000
 1-800-362-3550 www.3M.com/Sealants
 3M is a trademark of 3M Company.
 ©2016 3M. All rights reserved.