

Eaton 12TDLEJ50

Catalog Number: 12TDLEJ50

Eaton Bussmann series medium voltage DIN fuse, 50 A, AC 12 kV, 2", 51 x 292 mm, backup, DIN, with striker

General specifications



Product Name

Eaton Bussmann series medium voltage
DIN fuse

Catalog Number

12TDLEJ50

EAN

5027590516457

UPC

051712186100

Product Length/Depth

292 mm

Product Height

54 mm

Product Width

51 mm

Product Weight

1496 g

Compliances

DIN 43625

VDE 0670-4

IEC 60282-1

Certifications

UL

VDE

Product specifications

Used with

270303 Fuse clip

A3354710 Fuse clip

Type

Fuse

Special features

Back-up, Transformer protection, Indoor or outdoor use

Application

transformer protection

indoor or outdoor use

Amperage Rating

50 A

Fuse indicator

With Striker

Fuse size

51 x 292 mm

Breaking capacity

63 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

DIN

Utilization category

Other

Voltage type

Resources

Technical data sheets

720104 12kV DIN medium voltage fuses

720105 17.5kV DIN medium voltage fuses

720106 24kV DIN medium voltage fuses

AC

With striker

Yes

Class

Class back-up

Barrels

1

Construction type

Bolt-on

Pre arc (I²T)

2.8 x 1000

Resistance

13.5 Ohms

Watt losses

47 W

Fuse diameter

51 mm

Color

Brown

Interrupt rating

63 kAIC

Construction size

51 x 292 mm

Mounting method

Clip-in

Packaging type

Standard

Quantity

1

Voltage rating

12 kV

Fuse type

TDLEJ



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)