



Part Number : [191930266](#)

Product Description : VersaKrimp Ring Tongue Terminal for 4 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton

Series Number : 19193

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : F-366-38T



Documents & Resources

Drawings

[191930266 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 4 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton
Comments	Type I Non-insulated; Class 2
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753040595

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	9.415/g
Packaging Type	Carton

Stud Size	3/8" (M9)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	11.28mm max.
Wire Size (AWG)	4
Wire Size mm ²	25.00

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>190270172</u>
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>190270175</u>
Crimp Dies for 4 AWG Versakrimp Mylar Tape, use with Tape Crimp Module and TM-4000 Crimp Press	<u>190472220</u>