

FEATURES

- Galvanised steel construction
- Easy to inspect for damage
- Shock absorbing
- High resistance to abrasion
- Fatigue rated at 1 – times the working load limit at 20 000 cycles

RS PRO Eye Bolt M20 x 27mm

RS Stock No.: 673-664



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These Eye Bolts from our own RS PRO brand are intended for linear pulling loads in the direction of the thread. These Eye Bolts are proof tested and supplied complete with test certificate.

General Specifications

Type	Eye Bolt
Working Load Limit	1.6t
Material	Carbon Steel

Mechanical Specifications

Diameter	27mm
Thread Size	M20
Thread Length	32mm
Collar Diameter	40mm
Collar Thickness	14mm
Eye Outside Diameter	59mm
Overall Height	97mm
Applications	Tensioning wires, Securing loads

Safety Standard

Standards Met	BS 4278:1984
----------------------	--------------

