

Punch PG 13 / M 20 - 1 pc | System accessories - Knockout punch and dies

Article: 4932430842



- Suitable for mild steel and aluminium up to a thickness of 3 mm.
- Also suitable for stainless steel max. 2.5 mm.
- Draw stud bolt 49162680 (for 16.2 and 20.4 mm) \varnothing 11,1 mm: requires pre-drilling with \varnothing 11.3 - 11.5 mm drill bit / step drill.
- Draw stud bolt 49162681 \varnothing 19 mm: requires pre-drilling with \varnothing 19.5 - 20 mm drill bit / step drill.

Punch PG 13 / M 20 - 1 pc	
Standard PG size	PG 13.5
Standard ISO metric size	M 20
Diameter (mm)	20.4
Article Number	4932430842
Pack quantity	1