


Features

• Fun, versatile Smart LED strip lights with easy DIY installation, customizable colours, and dynamic effects to elevate home lighting and décor. Transform space with pre-set scenes and sync RGB lights with music for an immersive experience. More than 16 million colour combinations to choose from. Works effortlessly with SylSmart Home App, Amazon Alexa, Google Assistant, Siri Shortcuts and IR remote for seamless control and convenience. Adjustable brightness from 1% to 100% with wireless dimming function for perfect illumination. Quick and easy installation with 3M glue tape. Flexible and cuttable design for easy customization. Equipped with EU plug

Product Overview

Product name	SylStrip 5M RGBW SST UK
Lamp shape	Linear
Cap/Base	N/A
Lamp finish	None
Mount	Built-in
General application	Hospitality, Residential & Consumer, Retail
ETIM Class	EC002706
CRI (Ra)	80
Colour Variation Initial (SDCM)	N/A
Photobiological Risk Group	RG1
Wattage (W)	12
Power consumption (W)	12
Dimmable	Yes
IP rating	IP20
Product EAN number	5410288901077
Warranty	3 years
Useful luminous flux (#use)	750

Technical drawings



Data table

GENERAL DATA

Product name	SylStrip 5M RGBW SST UK
Lamp shape	Linear
Cap/Base	N/A
Lamp finish	None
Mount	Built-in
General application	Hospitality, Residential & Consumer, Retail
ETIM Class	EC002706
Warranty	3 years

OPTICAL DATA

Useful luminous flux (#use)	750
CRI (Ra)	80
Colour Variation Initial (SDCM)	N/A
Photobiological Risk Group	RG1

ELECTRICAL DATA

Power consumption (W)	12
Wattage (W)	12
Current (A)	0.02
Primary Supply/Product voltage - min (V)	220

SylStrip 5M RGBW SST UK 0090107

Primary Supply/Product voltage - max (V)	240
--	-----

Lamp power factor	0.5
-------------------	-----

Control gear required	Yes
-----------------------	-----

Dimmable	Yes
----------	-----

Inrush Current (A)	6.6
--------------------	-----

Inrush Duration (µs)	100
----------------------	-----

Lamp Energy Label (class)	G
---------------------------	---

LIFETIME DATA

Lifespan L70 B50	25000
------------------	-------

PHYSICAL DATA

IP rating	IP20
-----------	------

Nominal Product Length (mm)	5250
-----------------------------	------

Nominal Product Width (mm)	10
----------------------------	----

Nominal Product Height (mm)	3
-----------------------------	---

Weight (kg)	0.304
-------------	-------

PACKAGING

Product EAN number	5410288901077
--------------------	---------------

Packaging single length / height (cm)	14.1
---------------------------------------	------

Packaging single width (cm)	7.1
-----------------------------	-----

Packaging single depth (cm)	13.0
-----------------------------	------

DUN14 (inner)	15410288901074
---------------	----------------

Units per outer package	6
-------------------------	---

Packaging outer length / height (cm)	24.1
--------------------------------------	------

Packaging outer width (cm)	29.9
----------------------------	------

Packaging outer depth (cm)	15.8
----------------------------	------

SAFETY DATA

Special purpose lamp	No
----------------------	----

Dry applications use only	No
---------------------------	----

Suitable for household illumination	No
-------------------------------------	----

SYLVANIA

SylStrip 5M RGBW SST UK
0090107

Light your world