

PRODUCT-DETAILS

TCZ347

2/4WAY MNTG BASE 1.1X1.1IN ETFE SCR



General Information

Extended Product Type	TCZ347
Product ID	7TAG009820R0055
EAN	5414363059462
Catalog Description	2/4WAY MNTG BASE 1.1X1.1IN ETFE SCR
Long Description	Four-Way and Two-Way Mounting Base With Open Leg Design, Green ETFE for Temperatures up to 170 Degrees Celsius (338 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 8.5mm (0.33 Inches), Screw Mounting Method, #8 Screw, Mounting Hole Size of 4.4mm (0.17 Inches), Bulk Pack

Ordering

EAN	5414363059462
UPC	786210890494

Dimensions

Product Net Length	0, mm
--------------------	-------

Container Information

Package Level 1 Units	500 piece
Package Level 2 Units	5000 piece
Package Level 2 Width	13.4 in

	340 mm
Package Level 2 Height	9.5 in 241 mm
Package Level 2 Depth / Length	21 in 533 mm

Additional Information

Brand / Label	Ty-Rap
Color	Green
Effective Date	19770617
Material	Fluoropolymer
Mounting Type	Screw
Number of Batteries	0
Process Temperature Rating	-50 to +388 °F
Product Name	NYLON CABLE TIES AND ACCESSORIES
Product Type	Mounting Base
Special Functions	Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TCZ347
Instructions and Manuals	TCZ347
REACH Declaration	9AKK107992A8789
RoHS Information	9AKK107991A8363

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

