

0 603 102 070 – PMF 220 CE

Material number 0 603 102 070



EAN 3165140828505

Discount Group GMD

Baretool number 3 603 A02 070

BIM segment saw blade Wood and Metal,
85 mm, ACZ 85 EB
2 609 256 943 ✓

Delta sanding plate 93 mm, AVZ 93 G
2 609 256 956 ✓

Delta sanding sheet set
2 609 256 A54 ✓

Voltage 230 V

Technical data

Technical data

Power input	220 W
Power output	130 W
No-load speed	15.000 – 20.000 rpm
Oscillation angle on left/right	2,8 °
Weight	1,1 kg



Functions

Oscillation angle	✓
Bosch Electronic	✓

Noise/vibration information (w/o handle)

Sound pressure level	84 dB(A)
----------------------	----------

Noise level	The A-rated noise level of the power tool is typically as follows: Sound pressure level dB(A); Sound power level dB(A). Uncertainty K=dB.
-------------	---



Sound power level	95 dB(A)
Uncertainty K	3 dB
Noise level	The A-rated noise level of the power tool is typically as follows: Sound pressure level 84 dB(A); Sound power level 95 dB(A). Uncertainty K= 3 dB.

Noise/vibration information (with handle)

Sales information

Positioning

- The versatile all-rounder for comfortable handling

User benefit

- Versatile tool thanks to a wide range of innovative Bosch Starlock accessories
- Convenient, effortless changing of all accessories thanks to magnetic toolholder with universal screw
- Maintain an exact cutting depth using the 4-stage depth stop

Other features

- Precise and gentle plunge cutting due to rounded cutting edges of the plunge cut saw blades with Curved-Tec
- Consistently high performance even under load thanks to Bosch Constant Electronic
- Optimum guidance due to optional attachment of an auxiliary handle
- Faster work rate thanks to powerful 220 watt motor
- Continuously variable preselection of the oscillation rate enables you to gear your work towards the material and application