

# RATCHETING COMBINATION SPANNER AF R 13/16"



- A ratcheting ring and open ended spanner combined with the same size at each end
- Off set at 13° for easier use on flat surfaces
- TengTools hip grip design on the ring end for contact with the flat side of the fastening
- 72 teeth ratchet spanners giving a 5° increment between clicks
- Reversible ratchet mechanism with a flip reverse lever
- Ideal for rapid tightening and loosening of fastenings
- Chrome vanadium satin finish
- Manufactured to DIN ISO 1711-1 and ASME B107.100

Reversible Ratcheting Combination Spanner 13/16"

## General information

**Country of origin:** Taiwan  
**Barcode:** 5020385043077  
**Tariff code Europe:** 8204110000  
**ECCN US:** EAR99  
**ETIM:** EC002218  
**UNSPSC:** 27111705

## Dimensions

**Net weight (g):** 360  
**Length:** 290 mm

## Attributes

**Product type:** Combination Spanners  
**Material:** CrV  
**Certificates:** N/A  
**Size:** 13/16"  
**Number of teeth:** 72  
**Reverse direction:** Flip reverse lever  
**Flexible head:** No  
**Tethering facility:** No  
**Spanner type:** Regular  
**Ratcheting:** Yes  
**Unit of measurement:** AF  
**Jaw diameter:** 46.0  
**Jaw height (mm):** 9.0  
**Offset angle jaw (°):** 15  
**Ring diameter (mm):** 40.0  
**Ring height (mm):** 13.0  
**Offset angle ring (°):** 15

## Features

AF

Technical changes and errors may occur. 01-08-2024 19:51



**DESIGNED IN SWEDEN**

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3  
 441 39 Alingsås, Sweden