

Datasheet

# ispot® LED Driverless Bulkhead PIR



## Description

The ispot® driverless bulkhead PIR is the most advanced LED bulkhead on the market. It boasts an attractive ultra-thin design, with a depth of only 36mm. The ispot® driverless bulkhead PIR is vandal proof with no visible screws on the front. Tamper proof screws are hidden on the back. Available in daylight and warm white with a black or white finish.

## Features

- Innovative high voltage LED chips – no driver required
- Daylight (5700K) and warm white (3000K) options
- High grade aluminium body and polycarbonate diffuser
- Impact resistant
- No visible screws on front
- Built in daylight sensor
- PIR detection range 90°
- PIR detection distance 4m
- Available in black and white finishes
- 50,000 hours rated life
- 3 year guarantee
- IP65

## Range

ispot® Bulkhead PIR 10W 5700K WHITE	9185627
ispot® Bulkhead PIR 10W 5700K BLACK	9185620
ispot® Bulkhead PIR 20W 5700K BLACK	9185633
ispot® Bulkhead PIR 20W 5700K WHITE	9185624

## Standards

- BS EN 60598-1+A11
- BS EN 60598-2-1
- BS EN 60598-2-5
- BS EN 62471
- BS EN 62493
- BS EN 55015+A2
- BS EN 61547
- BS EN 61000-3-2+A2
- BS EN 61000-3-3

## Technical Specification

Voltage	100-240V~ 50/60Hz
Lamp	SMD LED
PIR distance	4m
PIR range	90°
Colour temp.	5700K / 3000K
IP rating	IP65

## Dimensions (mm), Beam Angle & Lumens

	Lumen Output	Beam Angle	Fitting Dimensions (L x H x D)
9185627	600lm	110°	220 x 130 x 36
9185620	600lm	110°	220 x 130 x 36
9185633	1200lm	110°	220 x 130 x 36
9185624	1200lm	110°	220 x 130 x 36