

## Features

- PVC Hook-up Wire
- UL 1007 Equivalent
- Tinned Copper Conductors

## RS PRO Hook Up Wire

RS Stock No.: 0217311



*Representative Image - Colour will vary*

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Stranded flexible Hook-up Wire designed for the internal cabling of electrical and electronic equipment. Suitable for a broad range of applications from control cabinets to specialist machine tools

Hook-up wire is a flexible cable with a durable PVC protective sheath and tinned copper conductors, available in multiple colours, ideal for colour-coding cable installations.

The cable offers good insulation due to the PVC insulation material and installation is easy and efficient thanks to the flexible layout of the cable.

## General Specifications

|                                |                     |
|--------------------------------|---------------------|
| Conductor                      | Tinned Copper       |
| Insulation                     | PVC                 |
| Insulation Colour              | Black               |
| Approximate Diameter           | 1.3 mm              |
| Number of conductors           | 1                   |
| Conductor cross sectional area | 26 AWG              |
| Conductor construction         | 7 strands of 0.16mm |
| Length                         | 305 MTRS            |

## Mechanical Specifications

|                     |        |
|---------------------|--------|
| Minimum temperature | -20°C  |
| Maximum temperature | +105°C |

## Electrical Specifications

|                |      |
|----------------|------|
| Voltage rating | 300V |
|----------------|------|