

Specifications

Eaton ESWH28

Eaton G3+ Switched Rack PDU, 1U, Inputs C20, 3.84 kW max, 16A, 200-240V, Outlets 8XC13



General specifications

PRODUCT NAME	Eaton Rack PDU G4
---------------------	-------------------

CATALOG NUMBER	ESWH28
-----------------------	--------

MODEL CODE	EPDU SW 1U (C20 16A 1P)8XC13
-------------------	------------------------------

EAN	3553340696190
------------	---------------

PRODUCT LENGTH/DEPTH	445 mm
-----------------------------	--------

PRODUCT HEIGHT	203 mm
-----------------------	--------

PRODUCT WIDTH	43 mm
----------------------	-------

PRODUCT WEIGHT	3.4 kg
-----------------------	--------

COMPLIANCES	RoHS Compliant EAC CE Marked
--------------------	------------------------------------

CERTIFICATIONS	IEC 60950-1 IEC 61000-6-2 IEC 61000-6-4
-----------------------	---



Powering Business Worldwide

Electrical input

INPUT CONNECTION	C20
WATTAGE	3.84 kW max
AMPERAGE RATING	16A
INPUT VOLTAGE	200-240V
PHASE	Single-phase
FREQUENCY RATING	50/60 Hz
CORD LENGTH	3m

Electrical output

OUTLETS	(8) C13
NUMBER OF OUTPUTS C13	8
NUMBER OF OUTLETS WITH EARTH PIN	8

Technology & communications

TYPE Switched Rack PDU

OUTLET CONTROL Yes

SPECIAL FEATURES

- Remote Site Management
- Turn off unused outlets to control commissioning
- Phase Metering, Circuit Breaker Current Metering and Input Metering
- Circuit Breaker Status Monitoring
- Outlet and IT Equipment Switching/reboot /sequencing across A and B feed in Daisy-Chain
- Sequence Outlets to avoid in-rush current, to ensure equipment starts in correct order
- Hot-Swap Control module with advanced LCD
- Optional Temperature/Humidity sensor
- Built-in IEC outlet eGrip retention, retains all standard IEC plugs
- Daisy-Chain up to 8 PDUs, reduce network infrastructure costs
- Power chain monitoring & Real time Intelligence on your Data Center, via Eaton Intelligent Power Manager

ETHERNET INTERFACE Yes

SERIAL INTERFACE Yes

SNMP Yes

COMMUNICATION HTTP, HTTPS, SSL, Telnet, FTP, SNMP, SMTP, DNS, DHCP, LDAP, RADIUS

MASS CONFIGURATION Yes

Additional specifications

OPERATING TEMPERATURE 0° to 60°C (32° to 140°F)

MATERIAL Aluminium

COLOR Black

Resources

	Eaton UPS Services Quick Guide - EN
BROCHURES	Eaton UPS and battery services - EN Eaton ePDU G3 - Brochure
COMPLIANCE INFORMATION	EU Declaration of Conformity Eaton ePDUs G3
DECLARATIONS OF CONFORMITY	EU declaration of conformity Rack PDU G4
DRAWINGS	ESWH28 sk-86819-y1
MANUALS AND USER GUIDES	Eaton ePDU G3 - Installation and Connectivity Quick Start

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

